























序号	品名	材质	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色:本色	X.±0.50	±1°	PART NO. BTB0877G-2*NPBL1	TITLE: 0.8 Pitch B型立式 BTB公座业务图(单高7.7)			
②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面点镀金	X.X±0.20						
③	0.8 Pitch B型立式 BTB公座吸盖	不锈钢	X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG			
			UNITS	mm					
③	0.8 Pitch B型立式 BTB公座吸盖	不锈钢	MATERILA	— — —	CHED: Olvia	 SCALE SHEET			
			FINISH	— — —	APPD: Ava				

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压： $100\text{V}, \text{AC}$ 。
4. 接触电阻： $\leq 0.05\Omega$ 。
5. 绝缘电阻： $\geq 500\text{M}\Omega$

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

公座 (PLUG) 母座 (SOCKET)				
				
				
				
				

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±1°	PART NO.		TITLE: 0.8 Pitch B型立式		
X.X±0.20		BTB0877G-2*NPBL1		BTB公座业务图(单高7.7)		
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	2/2