





技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻:  $\leq 0.02\Omega$ 。
5. 绝缘电阻:  $\geq 100M\Omega$ 。

| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |

| 序号 | 品名                          | 材质                      |
|----|-----------------------------|-------------------------|
| ①  | 0.8 Pitch E型<br>单槽侧插BTB公座胶芯 | LCP<br>UL94 V-0, 颜色: 本色 |
| ②  | 0.8 Pitch E型<br>单槽侧插BTB公座端子 | 铜合金 / 表面点镀金             |

| Part No           | CKT  | A     | B     | C     | D     |
|-------------------|------|-------|-------|-------|-------|
| BTB0835G-2*2PEC1  | 2*2  | 0.80  | 2.35  | 3.35  | 2.60  |
| BTB0835G-2*3PEC1  | 2*3  | 1.60  | 3.15  | 4.15  | 3.40  |
| BTB0835G-2*4PEC1  | 2*4  | 2.40  | 3.95  | 4.95  | 4.20  |
| BTB0835G-2*5PEC1  | 2*5  | 3.20  | 4.75  | 5.75  | 5.00  |
| BTB0835G-2*6PEC1  | 2*6  | 4.00  | 5.55  | 6.55  | 5.80  |
| BTB0835G-2*7PEC1  | 2*7  | 4.80  | 6.35  | 7.35  | 6.60  |
| BTB0835G-2*8PEC1  | 2*8  | 5.60  | 7.15  | 8.15  | 7.40  |
| BTB0835G-2*9PEC1  | 2*9  | 6.40  | 7.95  | 8.95  | 8.20  |
| BTB0835G-2*10PEC1 | 2*10 | 7.20  | 8.75  | 9.75  | 9.00  |
| BTB0835G-2*11PEC1 | 2*11 | 8.00  | 9.55  | 10.55 | 9.80  |
| BTB0835G-2*12PEC1 | 2*12 | 8.80  | 10.35 | 11.35 | 10.60 |
| BTB0835G-2*13PEC1 | 2*13 | 9.60  | 11.15 | 12.15 | 11.40 |
| BTB0835G-2*14PEC1 | 2*14 | 10.40 | 11.95 | 12.95 | 12.20 |
| BTB0835G-2*15PEC1 | 2*15 | 11.20 | 12.75 | 13.75 | 13.00 |
| BTB0835G-2*16PEC1 | 2*16 | 12.00 | 13.55 | 14.55 | 13.80 |
| BTB0835G-2*17PEC1 | 2*17 | 12.80 | 14.35 | 15.35 | 14.60 |
| BTB0835G-2*18PEC1 | 2*18 | 13.60 | 15.15 | 16.15 | 15.40 |
| BTB0835G-2*19PEC1 | 2*19 | 14.40 | 15.95 | 16.95 | 16.20 |
| BTB0835G-2*20PEC1 | 2*20 | 15.20 | 16.75 | 17.75 | 17.00 |
| .....             | ...  | ...   | ...   | ...   | ...   |
| BTB0835G-2*40PEC1 | 2*40 | 31.20 | 32.75 | 33.75 | 33.00 |

| TOLERANCE  |     | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                                            |       |       |
|------------|-----|--------------------------------------------------------------------|--------------------------------------------|-------|-------|
| X. ±0.50   | ±1° | PART NO.<br>BTB0835G-2*NPEC1                                       | TITLE: 0.8 Pitch E型单槽<br>侧插BTB公座业务图(单高3.5) |       |       |
| X.X ±0.20  |     |                                                                    |                                            |       |       |
| X.XX ±0.10 |     |                                                                    |                                            |       |       |
| UNITS      | mm  | DESIGN: Ethan                                                      | MANUFACTURE DWG                            |       |       |
| MATERILA   | --- | CHED: Olvia                                                        |                                            | SCALE | SHEET |
| FINISH     | --- | APPD: Ava                                                          |                                            | N:A   | 1/1   |