








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

台高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

Part No	CKT	A	B	C	D
BTB0526G-2*4PBL1	2X4	1.50	2.60	4.10	3.60
BTB0526G-2*5PBL1	2X5	2.00	3.10	4.60	4.10
BTB0526G-2*6PBL1	2X6	2.50	3.60	5.10	4.60
BTB0526G-2*7PBL1	2X7	3.00	4.10	5.60	5.10
BTB0526G-2*8PBL1	2X8	3.50	4.60	6.10	5.60
BTB0526G-2*9PBL1	2X9	4.00	5.10	6.60	6.10
BTB0526G-2*10PBL1	2X10	4.50	5.60	7.10	6.60
BTB0526G-2*11PBL1	2X11	5.00	6.10	7.60	7.10
BTB0526G-2*12PBL1	2X12	5.50	6.60	8.10	7.60
BTB0526G-2*13PBL1	2X13	6.00	7.10	8.60	8.10
BTB0526G-2*14PBL1	2X14	6.50	7.60	9.10	8.60
BTB0526G-2*15PBL1	2X15	7.00	8.10	9.60	9.10
BTB0526G-2*16PBL1	2X16	7.50	8.60	10.10	9.60
BTB0526G-2*17PBL1	2X17	8.00	9.10	10.60	10.10
BTB0526G-2*18PBL1	2X18	8.50	9.60	11.10	10.60
BTB0526G-2*19PBL1	2X19	9.00	10.10	11.60	11.10
BTB0526G-2*20PBL1	2X20	9.50	10.60	12.10	11.60
BTB0526G-2*22PBL1	2X22	10.50	11.60	13.10	12.60
BTB0526G-2*25PBL1	2X25	12.00	13.10	14.60	14.10
BTB0526G-2*30PBL1	2X30	14.50	15.60	17.10	16.60
BTB0526G-2*35PBL1	2X35	17.00	18.10	19.60	19.10
BTB0526G-2*40PBL1	2X40	19.50	20.60	22.10	21.60



序号	品名	材质	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
①	0.5 Pitch B型 单槽立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色	X.±0.50	±1°	PART NO. BTB0526G-2*NPBL1	TITLE: 0.5 Pitch B型单槽立式 BTB公座业务图(单高2.6)无焊片镀点金			
			X.X±0.20						
			X.XX±0.10						
②	0.5 Pitch B型 单槽立式BTB公座端子	铜合金/表面点镀金	UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG			
			MATERILA	---	CHED: Olvia		SCALE N:A	SHEET 1/1	
			FINISH	---	APPD: Ava				