





1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: $125\text{V}, \text{AC}$.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$

Part No	CKT	A	B	C	D	E
BTB0820G-2*4PAL1	2*4	2.40	3.45	5.10	4.20	4.00
BTB0820G-2*5PAL1	2*5	3.20	4.25	5.90	5.00	
BTB0820G-2*6PAL1	2*6	4.00	5.05	6.70	5.80	
BTB0820G-2*7PAL1	2*7	4.80	5.85	7.50	6.60	
BTB0820G-2*8PAL1	2*8	5.60	6.65	8.30	7.40	
BTB0820G-2*9PAL1	2*9	6.40	7.45	9.10	8.20	
BTB0820G-2*10PAL1	2*10	7.20	8.25	9.90	9.00	
BTB0820G-2*11PAL1	2*11	8.00	9.05	10.70	9.80	
BTB0820G-2*12PAL1	2*12	8.80	9.85	11.50	10.60	
BTB0820G-2*13PAL1	2*13	9.60	10.65	12.30	11.40	
BTB0820G-2*14PAL1	2*14	10.40	11.45	13.10	12.20	8.00
BTB0820G-2*15PAL1	2*15	11.20	12.25	13.90	13.00	
BTB0820G-2*16PAL1	2*16	12.00	13.05	14.70	13.80	
BTB0820G-2*17PAL1	2*17	12.80	13.85	15.50	14.60	
BTB0820G-2*18PAL1	2*18	13.6	14.65	16.30	15.40	
BTB0820G-2*19PAL1	2*19	14.40	15.45	17.10	16.20	
BTB0820G-2*20PAL1	2*20	15.20	16.25	17.90	17.00	
BTB0820G-2*22PAL1	2*22	16.80	17.85	19.50	18.60	
BTB0820G-2*25PAL1	2*25	19.20	20.25	21.90	21.00	
BTB0820G-2*30PAL1	2*30	23.20	24.25	25.90	25.00	
BTB0820G-2*35PAL1	2*35	27.20	28.25	29.90	29.00	
BTB0820G-2*40PAL1	2*40	31.20	32.25	33.90	33.00	
BTB0820G-2*50PAL1	2*50	39.20	40.25	41.90	41.00	

序号	品名	材质	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
①	0.8 Pitch双槽立式 BTB公座嵌芯	PA10T UL94 V-0, 颜色:黑色	X.±0.50	±1°	PART NO. BTB0820G-2*NPAL1	TITLE: 0.8 Pitch双槽立式 BTB公座业务图(单高2.0)		
			X.X±0.20					
②	0.8 Pitch双槽立式 BTB公座端子	铜合金/表面点镀金	X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
			UNITS	mm				
③	0.8 Pitch双槽立式 BTB公座吸盖	LCP UL94 V-0, 颜色:黑色	MATERILA	— — —	CHED: Olvia		SCALE	SHEET
			FINISH	— — —	APPD: Ava		N:A	1/1