




SECTION A-A



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$ 。

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

序号	品名	材质
①	0.8 Pitch E型 单槽侧插BTB母座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch E型 单槽侧插BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
BTB0851M-2*2PEC1	2*2	0.80	2.45	3.60	2.60
BTB0851M-2*3PEC1	2*3	1.60	3.25	4.40	3.40
BTB0851M-2*4PEC1	2*4	2.40	4.05	5.20	4.20
BTB0851M-2*5PEC1	2*5	3.20	4.85	6.00	5.00
BTB0851M-2*6PEC1	2*6	4.00	5.65	6.80	5.80
BTB0851M-2*7PEC1	2*7	4.80	6.45	7.60	6.60
BTB0851M-2*8PEC1	2*8	5.60	7.25	8.40	7.40
BTB0851M-2*9PEC1	2*9	6.40	8.05	9.20	8.20
BTB0851M-2*10PEC1	2*10	7.20	8.85	10.00	9.00
BTB0851M-2*11PEC1	2*11	8.00	9.65	10.80	9.80
BTB0851M-2*12PEC1	2*12	8.80	10.45	11.60	10.60
BTB0851M-2*13PEC1	2*13	9.60	11.25	12.40	11.40
BTB0851M-2*14PEC1	2*14	10.40	12.05	13.20	12.20
BTB0851M-2*15PEC1	2*15	11.20	12.85	14.00	13.00
BTB0851M-2*16PEC1	2*16	12.00	13.65	14.80	13.80
BTB0851M-2*17PEC1	2*17	12.80	14.45	15.60	14.60
BTB0851M-2*18PEC1	2*18	13.60	15.25	16.40	15.40
BTB0851M-2*19PEC1	2*19	14.40	16.05	17.20	16.20
BTB0851M-2*20PEC1	2*20	15.20	16.85	18.00	17.00
.....	...	...	...	...	...
BTB0851M-2*40PEC1	2*40	31.20	32.85	34.00	33.00

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. BTB0851M-2*NPEC1	TITLE: 0.8 Pitch E型单槽 侧插BTB母座业务图(单高5.1)		
X.X±0.20			MANUFACTURE DWG		
X.XX±0.10					
UNITS	mm	DESIGN: Ethan		SCALE	SHEET
MATERILA	---	CHED: Olvia		N:A	1/1
FINISH	---	APPD: Ava			