








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

序号	品名	材质
①	0.5 Pitch B型 单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型 单槽立式BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
BTB0544M-2*5PBL1	2X5	2.00	3.20	4.70	4.10
BTB0544M-2*6PBL1	2X6	2.50	3.70	5.20	4.60
BTB0544M-2*7PBL1	2X7	3.00	4.20	5.70	5.10
BTB0544M-2*8PBL1	2X8	3.50	4.70	6.20	5.60
BTB0544M-2*9PBL1	2X9	4.00	5.20	6.70	6.10
BTB0544M-2*10PBL1	2X10	4.50	5.70	7.20	6.60
BTB0544M-2*11PBL1	2X11	5.00	6.20	7.70	7.10
BTB0544M-2*12PBL1	2X12	5.50	6.70	8.20	7.60
BTB0544M-2*13PBL1	2X13	6.00	7.20	8.70	8.10
BTB0544M-2*14PBL1	2X14	6.50	7.70	9.20	8.60
BTB0544M-2*15PBL1	2X15	7.00	8.20	9.70	9.10
BTB0544M-2*16PBL1	2X16	7.50	8.70	10.20	9.60
BTB0544M-2*17PBL1	2X17	8.00	9.20	10.70	10.10
BTB0544M-2*18PBL1	2X18	8.50	9.70	11.20	10.60
BTB0544M-2*19PBL1	2X19	9.00	10.20	11.70	11.10
BTB0544M-2*20PBL1	2X20	9.50	10.70	12.20	11.60
BTB0544M-2*22PBL1	2X22	10.50	11.70	13.20	12.60
BTB0544M-2*25PBL1	2X25	12.00	13.20	14.70	14.10
BTB0544M-2*30PBL1	2X30	14.50	15.70	17.20	16.60
BTB0544M-2*35PBL1	2X35	17.00	18.20	19.70	19.10
BTB0544M-2*40PBL1	2X40	19.50	20.70	22.20	21.60

合高(H)	公座单高	母座单高	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
3.0	2.2	2.2	X.±0.50	±1°	PART NO. BTB0544M-2*NPBL1	TITLE: 0.5 Pitch B型单槽立式 BTB母座业务图(单高4.4)无焊片镀点金			
3.5	2.2	2.7	X.X±0.20						
			X.XX±0.10						
4.0	2.2	3.2	UNITS	mm	DESIGN: Ethan		MANUFACTURE DWG		
			MATERILA	— — —	CHED: Olvia				
5.0	2.6	4.4	FINISH	— — —	APPD: Ava		SCALE	SHEET	
							N:A	1/1	