







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

序号	品名	材质		
①	0.8 Pitch F型 单槽立式BTB公座胶芯	PA9T UL94 V-O,颜色:黑色		
②	0.8 Pitch F型 单槽立式公座端子	铜合金/表面点镀金		
总高(H)	公座单高(H)		母座单高(H)	
	H	H1		
	4.00	2.80	1.80	2.90
	4.50	3.30		
	5.00	3.80		
	5.50	4.30	2.30	3.40
	6.00	4.80		
	6.50	5.30		
	7.00			
			3.90	

Part No	CKT	A	B	C	D
BTB0833G-2*3PFL1	2*3	4.30	2.80	1.60	3.40
BTB0833G-2*4PFL1	2*4	5.10	3.60	2.40	4.20
BTB0833G-2*5PFL1	2*5	5.90	4.40	3.20	5.00
BTB0833G-2*6PFL1	2*6	6.70	5.20	4.00	5.80
BTB0833G-2*7PFL1	2*7	7.50	6.00	4.80	6.60
BTB0833G-2*8PFL1	2*8	8.30	6.80	5.60	7.40
BTB0833G-2*9PFL1	2*9	9.10	7.60	6.40	8.20
BTB0833G-2*10PFL1	2*10	9.90	8.40	7.20	9.00
BTB0833G-2*15PFL1	2*15	13.90	12.40	11.20	13.00
BTB0833G-2*20PFL1	2*20	17.90	16.40	15.20	17.00
BTB0833G-2*25PFL1	2*25	21.90	20.40	19.20	21.00
BTB0833G-2*30PFL1	2*30	25.90	24.40	23.20	25.00
BTB0833G-2*35PFL1	2*35	29.90	28.40	27.20	29.00
BTB0833G-2*40PFL1	2*40	33.90	32.40	31.20	33.00
BTB0833G-2*45PFL1	2*45	37.90	36.40	35.20	37.00
BTB0833G-2*50PFL1	2*50	41.90	40.40	39.20	41.00

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. BTB0833G-2*NPFL1	TITLE: 0.8 Pitch F型单槽 立式BTB公座业务图(单高3.3)		
X.X±0.20					
X.XX±0.10					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	---	CHED: Olvia		SCALE	SHEET
FINISH	---	APPD: Ava		N:A	1/1