








| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻:  $\leq 0.02\Omega$ 。
5. 绝缘电阻:  $\geq 1000M\Omega$ 。



| 序号    | 品名                          | 材质                       |
|-------|-----------------------------|--------------------------|
| ①     | 0.8 Pitch F型<br>单槽立式BTB母座胶芯 | PA9T<br>UL94 V-0, 颜色: 黑色 |
| ②     | 0.8 Pitch F型<br>单槽立式母座端子    | 铜合金/表面点镀金                |
| ③     | 0.8 Pitch B型<br>单槽立式BTB麦拉   | 耐高温不干胶                   |
| 总高(H) |                             | 公座单高(H1)                 |
| 4.00  |                             | 2.80                     |
| 4.50  |                             | 3.30                     |
| 5.00  |                             | 3.80                     |
| 5.50  |                             | 4.30                     |
| 6.00  |                             | 4.80                     |
| 6.50  |                             | 5.30                     |
| 7.00  |                             | 5.80                     |
|       |                             | 母座单高(H2)                 |
|       |                             | 2.90                     |
|       |                             | 3.40                     |
|       |                             | 3.90                     |

| Part No           | CKT  | A     | B     | C     | D     |
|-------------------|------|-------|-------|-------|-------|
| BTB0829M-2*3PFL1  | 2*3  | 4.30  | 2.80  | 1.60  | 3.40  |
| BTB0829M-2*4PFL1  | 2*4  | 5.10  | 3.60  | 2.40  | 4.20  |
| BTB0829M-2*5PFL1  | 2*5  | 5.90  | 4.40  | 3.20  | 5.00  |
| BTB0829M-2*6PFL1  | 2*6  | 6.70  | 5.20  | 4.00  | 5.80  |
| BTB0829M-2*7PFL1  | 2*7  | 7.50  | 6.00  | 4.80  | 6.60  |
| BTB0829M-2*8PFL1  | 2*8  | 8.30  | 6.80  | 5.60  | 7.40  |
| BTB0829M-2*9PFL1  | 2*9  | 9.10  | 7.60  | 6.40  | 8.20  |
| BTB0829M-2*10PFL1 | 2*10 | 9.90  | 8.40  | 7.20  | 9.00  |
| BTB0829M-2*15PFL1 | 2*15 | 13.90 | 12.40 | 11.20 | 13.00 |
| BTB0829M-2*20PFL1 | 2*20 | 17.90 | 16.40 | 15.20 | 17.00 |
| BTB0829M-2*25PFL1 | 2*25 | 21.90 | 20.40 | 19.20 | 21.00 |
| BTB0829M-2*30PFL1 | 2*30 | 25.90 | 24.40 | 23.20 | 25.00 |
| BTB0829M-2*35PFL1 | 2*35 | 29.90 | 28.40 | 27.20 | 29.00 |
| BTB0829M-2*40PFL1 | 2*40 | 33.90 | 32.40 | 31.20 | 33.00 |
| BTB0829M-2*45PFL1 | 2*45 | 37.90 | 36.40 | 35.20 | 37.00 |
| BTB0829M-2*50PFL1 | 2*50 | 41.90 | 40.40 | 39.20 | 41.00 |

| TOLERANCE |     | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                                            |       |       |
|-----------|-----|--------------------------------------------------------------------|--------------------------------------------|-------|-------|
| X.±0.50   | ±1° | PART NO.<br>BTB0829M-2*NPFL1                                       | TITLE: 0.8 Pitch F型单槽<br>立式BTB母座业务图(单高2.9) |       |       |
| X.X±0.20  |     |                                                                    |                                            |       |       |
| X.XX±0.10 |     |                                                                    |                                            |       |       |
| UNITS     | mm  | DESIGN: Ethan                                                      | MANUFACTURE DWG                            |       |       |
| MATERILA  | --- | CHED: Olvia                                                        |                                            | SCALE | SHEET |
| FINISH    | --- | APPD: Ava                                                          |                                            | N:A   | 1/1   |