







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




High photosynthesis 合高 (H)	The female seat neight 母座高度 (H1)	The male seat neight 公座高度 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D
BTB0522M-2*4PAL2	2*4	1.50	2.55	4.70	4.00
BTB0522M-2*5PAL2	2*5	2.00	3.05	5.20	
BTB0522M-2*6PAL2	2*6	2.50	3.55	5.70	
BTB0522M-2*7PAL2	2*7	3.00	4.05	6.20	
BTB0522M-2*8PAL2	2*8	3.50	4.55	6.70	
BTB0522M-2*9PAL2	2*9	4.00	5.05	7.20	
BTB0522M-2*10PAL2	2*10	4.50	5.55	7.70	
BTB0522M-2*11PAL2	2*11	5.00	6.05	8.20	
BTB0522M-2*12PAL2	2*12	5.50	6.55	8.70	
BTB0522M-2*13PAL2	2*13	6.00	7.05	9.20	
BTB0522M-2*14PAL2	2*14	6.50	7.55	9.70	8.00
BTB0522M-2*15PAL2	2*15	7.00	8.05	10.20	
BTB0522M-2*16PAL2	2*16	7.50	8.55	10.70	
BTB0522M-2*17PAL2	2*17	8.00	9.05	11.20	
BTB0522M-2*18PAL2	2*18	8.50	9.55	11.70	
BTB0522M-2*19PAL2	2*19	9.00	10.05	12.20	
BTB0522M-2*20PAL2	2*20	9.50	10.55	12.70	
BTB0522M-2*22PAL2	2*22	10.50	11.05	13.70	
BTB0522M-2*25PAL2	2*25	12.00	13.05	15.20	
BTB0522M-2*30PAL2	2*30	14.50	15.55	17.70	
BTB0522M-2*35PAL2	2*35	17.00	18.05	20.20	
BTB0522M-2*40PAL2	2*40	19.50	20.55	22.70	
BTB0522M-2*50PAL2	2*50	24.50	25.55	27.70	



适用线路板

序号	品名	材质	TOLERANCE	深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
①	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色:黑色	X.±0.50 ±1° X.X±0.20 X.XX±0.10	PART NO.	TITLE:		
②	0.5 Pitch双槽立式BTB母座端子	铜合金/表面点镀金	UNITS mm	BTB0522M-2*NPAL2	0.5 Pitch双槽立式BTB无柱母座(单高2.2)		
③	0.5 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0颜色:黑色.	MATERILA ---	DESIGN: Ethan	MANUFACTURE DWG		
			FINISH ---	CHED: Olvia			
				APPD: Ava			
					SCALE N:A	SHEET 1/1	