







High photosynthesis 含藻 (H)	The female seat neight 女座身高 (H1)	The male seat neight 公座身高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTB0540M-2*4PAL1	2*4	1.50	2.55	4.70	3.40	4.00
BTB0540M-2*5PAL1	2*5	2.00	3.05	5.20	3.90	
BTB0540M-2*6PAL1	2*6	2.50	3.55	5.70	4.40	
BTB0540M-2*7PAL1	2*7	3.00	4.05	6.20	4.90	
BTB0540M-2*8PAL1	2*8	3.50	4.55	6.70	5.40	
BTB0540M-2*9PAL1	2*9	4.00	5.05	7.20	5.90	
BTB0540M-2*10PAL1	2*10	4.50	5.55	7.70	6.40	
BTB0540M-2*11PAL1	2*11	5.00	6.05	8.20	6.90	
BTB0540M-2*12PAL1	2*12	5.50	6.55	8.70	7.40	
BTB0540M-2*13PAL1	2*13	6.00	7.05	9.20	7.90	
BTB0540M-2*14PAL1	2*14	6.50	7.55	9.70	8.40	
BTB0540M-2*15PAL1	2*15	7.00	8.05	10.20	8.90	
BTB0540M-2*16PAL1	2*16	7.50	8.55	10.70	9.40	
BTB0540M-2*17PAL1	2*17	8.00	9.05	11.20	9.90	
BTB0540M-2*18PAL1	2*18	8.50	9.55	11.70	10.40	8.00
BTB0540M-2*19PAL1	2*19	9.00	10.05	12.20	10.90	
BTB0540M-2*20PAL1	2*20	9.50	10.55	12.70	11.40	
BTB0540M-2*22PAL1	2*22	10.50	11.05	13.70	12.40	
BTB0540M-2*25PAL1	2*25	12.00	13.05	15.20	13.90	
BTB0540M-2*30PAL1	2*30	14.50	15.55	17.70	16.40	
BTB0540M-2*35PAL1	2*35	17.00	18.05	20.20	18.90	
BTB0540M-2*40PAL1	2*40	19.50	20.55	22.70	21.40	
BTB0540M-2*50PAL1	2*50	24.50	25.55	27.70	26.40	

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: $50\text{V}, \text{AC}$.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$

