







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 100V, AC。
4. 接触电阻: $\leq 0.05\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。

Part No	CKT	A	B	C
BTB08117M-2*10PBL1	2*10	7.20	13.80	12.20
BTB08117M-2*11PBL1	2*11	8.00	14.60	13.00
BTB08117M-2*12PBL1	2*12	8.80	15.40	13.80
BTB08117M-2*13PBL1	2*13	9.60	16.20	14.60
BTB08117M-2*14PBL1	2*14	10.40	17.00	15.40
BTB08117M-2*15PBL1	2*15	11.20	17.80	16.20
BTB08117M-2*16PBL1	2*16	12.00	18.60	17.00
BTB08117M-2*17PBL1	2*17	12.80	19.40	17.80
BTB08117M-2*18PBL1	2*18	13.60	20.20	18.60
BTB08117M-2*19PBL1	2*19	14.40	21.00	19.40
BTB08117M-2*20PBL1	2*20	15.20	21.80	20.20
BTB08117M-2*21PBL1	2*21	16.00	22.60	21.00
BTB08117M-2*22PBL1	2*22	16.80	23.40	21.80
BTB08117M-2*23PBL1	2*23	17.60	24.20	22.60
BTB08117M-2*24PBL1	2*24	18.40	25.00	23.40
BTB08117M-2*25PBL1	2*25	19.20	25.80	24.20
.....	...	...	...	...
BTB08117M-2*100PBL1	2*100	79.20	85.80	84.20

序号	品名	材质	TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
①	0.8 Pitch B型立式 BTB母座胶芯	LCP UL94 V-0, 颜色:本色	X.±0.50	±1°	PART NO. BTB08117M-2*NPBL1	TITLE: 0.8 Pitch B型立式 BTB母座业务图(单高11.7)			
			X.X±0.20						
			X.XX±0.10						
②	0.8 Pitch B型立式 BTB母座端子	铜合金/表面点镀金	UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG			
③	0.8 Pitch B型立式 BTB母座吸盖	不锈钢	MATERILA	— — —	CHED: Olvia	 SCALE SHEET			
			FINISH	— — —	APPD: Ava				

