







High photosynthesis 台高 (H)	The female seat height 女性座高 (H1)	The male seat height 男性座高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90




1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。

3. 额定电压: 50V, AC.

4. 接触电阻: $\leq 0.02 \Omega$.

5. 绝缘电阻: $\geq 100M\Omega$



序号	品名	材质	TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
①	0.5 Pitch双槽立式 BTB母座胶芯	PA10T UL94 V-0 颜色:黑色	X.±0.50	±1°	PART NO. BTB0530M-2*NPAL1	TITLE: 0.5 Pitch双槽立式BTB母(单高3.0)		
②	0.5 Pitch双槽立式 BTB母座端子	铜合金/表面点镀金	X.X±0.20					
			X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
			UNITS	mm	CHED: Olivia			
③	0.5 Pitch双槽立式 BTB母座吸盖	LCP UL94 V-0颜色:黑色.	MATERILA	— — —	APPD: Ava		SCALE	SHEET
			FINISH	— — —			N:A	1/1