




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

序号	品名	材质
①	0.5 Pitch D型 单槽侧插BTB公座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.5 Pitch D型 单槽侧插BTB公座端子	铜合金 / 表面点镀金

Part No	CKT	A	B	C	D
BTB0533G-2*2PDC1	2*2	0.50	2.50	2.50	1.70
BTB0533G-2*3PDC1	2*3	1.00	3.00	3.00	2.20
BTB0533G-2*4PDC1	2*4	1.50	3.50	3.50	2.70
BTB0533G-2*5PDC1	2*5	2.00	4.00	4.00	3.20
BTB0533G-2*6PDC1	2*6	2.50	4.50	4.50	3.70
BTB0533G-2*7PDC1	2*7	3.00	5.00	5.00	4.20
BTB0533G-2*8PDC1	2*8	3.50	5.50	5.50	4.70
BTB0533G-2*9PDC1	2*9	4.00	6.00	6.00	5.20
BTB0533G-2*10PDC1	2*10	4.50	6.50	6.50	5.70
BTB0533G-2*11PDC1	2*11	5.00	7.00	7.00	6.20
BTB0533G-2*12PDC1	2*12	5.50	7.50	7.50	6.70
BTB0533G-2*13PDC1	2*13	6.00	8.00	8.00	7.20
BTB0533G-2*14PDC1	2*14	6.50	8.50	8.50	7.70
BTB0533G-2*15PDC1	2*15	7.00	9.00	9.00	8.20
BTB0533G-2*16PDC1	2*16	7.50	9.50	9.50	8.70
BTB0533G-2*17PDC1	2*17	8.00	10.00	10.00	9.20
BTB0533G-2*18PDC1	2*18	8.50	10.50	10.50	9.70
BTB0533G-2*19PDC1	2*19	9.00	11.00	11.00	10.20
BTB0533G-2*20PDC1	2*20	9.50	11.50	11.50	10.70
...	...	...	...	...	...
BTB0533G-2*40PDC1	2*40	19.50	21.50	21.50	20.70

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X. ±0.50	±1°	PART NO. BTB0533G-2*NPDC1	TITLE: 0.5 Pitch D型单槽侧插BTB公座业务图(单高3.3)		
X.X ±0.20					
X.XX ±0.10					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	---	CHED: Olvia		SCALE	SHEET
FINISH	---	APPD: Ava		N:A	1/1