




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24

- SPECIFICATIONS
- Current rating: 3A AC, DC
 - Temperature range: -25°C ~ +85°C
 - Insulation resistance: 1000MΩ Min.
 - Withstanding voltage: 800V AC/ minute.
 - Contact resistance: 10mΩ Max.


Material:
Insulator Material:PA9T (UL 94V-0)
Pin Material:Brass
Contact Area Plating: TIN-Plating
Mate with: P2020 series header

Ordering Code:


M2020VS-2xNP
1 2

- 1.序列号
2.Pin位数:2x02P
2x20P

No. of Pins/Row	Dimension	
	A	B
2x02	6.00	2.00
2x03	8.00	4.00
2x04	10.00	6.00
2x05	12.00	8.00
2x06	14.00	10.00
2x07	16.00	12.00
2x08	18.00	14.00
2x09	20.00	16.00
2x10	22.00	18.00
2x11	24.00	20.00
2x12	26.00	22.00
2x13	28.00	24.00
2x14	30.00	26.00
2x15	32.00	28.00
2x16	34.00	30.00
2x17	36.00	32.00
2x18	38.00	34.00
2x19	40.00	36.00
2x20	42.00	38.00



2P 视图



2x02P-2x10P 0.10mm
2x11P-2x20P 0.15mm

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: M2020VS-2xNP		XFCN 兴飞连接器		
TITLE: 2.00mm Crimp Style Connectors		0769-82001899		
		www.xfconn.com		
		DWG NO: /		
APPD	Chen ZhiQiang	VIEW		
CHKD	Liu Wei	SCALE	SHEET	REV
DRAW	Chen HongJiang			
DATE	2024.07.26	NONE	1/1	A1