


Common Mode Filter

◆ Dimensions(Unit:mm):



A	B	C	D	E	F	G	H
13.7±0.3	10.4±0.3	15.2±0.3	6.3±0.3	5.3±0.3	3.0±0.5	0.95Ref	3.05Ref

◆ Schematics



◆ Electrical Characteristics:

Item	Spec	Test FRE
Z(Ω)	160Typ	100MHz/0.25V
DCR(mΩ)	0.3Max	25°C ± 3°C RH: 65%
Idc(A)	75.0 Max	
	ΔT≤40°C Typ	

◆ ELECTRICAL CHARACTERISTIC:

TEST ITEM	L(Ω)	DCR(m Ω)
TEST CONDITION	100MHZ/0.25V	25°C (REF.) RH: 65% (REF.)
SPEC	160 $\pm$ 25%	0.3 Max.
01	175	0.27
02	165	0.25
03	171	0.26
04	171	0.25
05	175	0.24
06	166	0.25
07	176	0.25
08	165	0.26
09	168	0.26
10	164	0.27
$\overline{X}$	169.6	0.253
R	11	0.02