


1 Product Identification

GDPZ 3216 M 300 3A0 T F
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Product Symbol
- ② Dimensions
- ③ Material Code
- ④ Impedance (300: 30Ω)
- ⑤ IR* (3A0: 3.0A)
- ⑥ Packaging Style (B: Bulk; T: Tape & Reel)
- ⑦ Lead Free

2 Appearance, Dimensions





Type	Dimensions (mm) [inch]			
	L	W	T	a1, a2
3216 (1206)	3.2±0.20	1.6±0.20	0.8±0.20	0.50±0.30

3 Rating


Operating Temperature Range : -55 to +125℃

Part No.	Impedance(Ω)	Test Freq. (MHz)	RDC (Ω) max	IR*(mA) max
GDPZ3216M260-6A0TF	26 $\pm$ 25%	100	0.012	6000
GDPZ3216M300-3A0TF	30 $\pm$ 25%	100	0.030	3000
GDPZ3216M500-6A0TF	50 $\pm$ 25%	100	0.012	6000
GDPZ3216M600-6A0TF	60 $\pm$ 25%	100	0.012	6000
GDPZ3216M800-3A0TF	80 $\pm$ 25%	100	0.040	3000
GDPZ3216M800-6A0TF	80 $\pm$ 25%	100	0.020	6000
GDPZ3216M121-3A0TF	121 $\pm$ 25%	100	0.045	3000
GDPZ3216M221-3A0TF	220 $\pm$ 25%	100	0.050	3000
GDPZ3216M221-4A0TF	220 $\pm$ 25%	100	0.030	4000
GDPZ3216M301-3A0TF	300 $\pm$ 25%	100	0.045	3000
GDPZ3216M601-3A0TF	600 $\pm$ 25%	100	0.070	3000
GDPZ3216M102-2A0TF	1000 $\pm$ 25%	100	0.090	2000


4 Curve




GDPZ3216M500-6A0TF




GDPZ3216M600-6A0TF




GDPZ3216M800-3A0TF




GDPZ3216M800-6A0TF




GDPZ3216M121-3A0TF




GDPZ3216M221-3A0TF




GDPZ3216M221-4A0TF




GDPZ3216M301-3A0TF



GDPZ3216M601-3A0TF




GDPZ3216M102-2A0TF




5 Packaging

(1) Dimensions of Reel (mm)



(2) Dimensions of Tape (mm):



W	A0	B0	K0	P	F	E	D	P0	P2	t	Packaging quantity
8.0 ± 0.3	1.9 ± 0.03	3.45 ± 0.03	0.95 ± 0.1	4.0 ± 0.05	3.5 ± 0.1	1.75 ± 0.1	1.5+ 0.1/-0.0	4.0 ± 0.1	2.0 ± 0.1	0.95 ± 0.03	4000PCS/REEL