






PCB 参考安装方式

NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M4 (M5, M6)
压线螺孔M4 (M5, M6) 可定制
- 3.Current Rating: 80A
额定电流:80A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 1.47Nm

Ordering Information

HC - * ** * - **** - * ** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	Welding Feet	Product No.	Material
HC=Hole (抽牙) W=Wire (压线螺孔) G=Gasket (垫片)	0.5~1.0mm 1.0~1.5mm 1.5~2.0mm 2.0~2.5mm 2.5~3.0mm 3.0~3.5mm	M3 (螺牙) M4 (螺牙) M5 (螺牙) M6 (螺牙) M8 (螺牙) M10 (螺牙)	2~3个 2~3个 2~3个 2~3个 2~3个 2~3个	010080808mm 1620~18.20mm	W=Hole (抽牙) W=Wire (压线螺孔) W=Flag (标识)	产品序号	默认=铜 (黄铜) W=Red Copper (紫铜)



			GENERAL TOLERANCE	制 图 DRAWING	07				深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL	审 核 CHECK				产品名称 TITLE	PCB 焊接端子 厚度1.2 贴片 抽牙 M4 4焊脚 30x10x7.9mm	版 本 REV.	A
			5 or more ±0.35	批 准 APPROVAL				产品料号 PART NO.	HC-M1244-3010-S537-07	单 位 UNITS	mm
1		初版发行	2~5 ±0.25	比 例 SCALE							
			0~2 ±0.15	投 影 Projection				材 料 MATERIAL		页 次 SHEET	1/1
序号 No.		变更内容 MODIFY CONTENT	日期 MODIFY DATE								