






- NOTES:
备注
- 1.Brass or purple copper,tin-plating
黄铜或紫铜, 镀锡
 - 2.Wire screw hole M5 (M4, M6)
压线螺孔M5 (M4, M6) 可定制
 - 3.Current Rating: 120A
额定电流:120A
 - 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
 - 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
 - 6.扭矩: 2.03 Nm

Ordering Information									
HC - * ** * - **** - D *** * - 07									
Type (Type) Full Tooth (全齿) Wire Nut (线螺母) Wire Gasket (线垫片)	Thickness (厚度) 0.8mm 1.0mm 1.2mm 1.5mm 2.0mm 2.5mm 3.0mm	Screw Thread (螺钉) M4 M5 M6	Welding Feet (焊脚) 2mm 4mm 6mm 8mm	Series (系列) 0808x8mm 1620x1620mm	(DIP) SMT Tag Dip	Product No. (产品序号)	Material (材料) Copper (铜) Purple Copper (紫铜)		



GENERAL TOLERANCE		制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
DIM TOL		审核		产品名称	PCB 焊接端子 厚度1.2 插板 抽牙	版本	A
5 or more ±0.35		批准		TITLE	M5 4焊脚 25x10x7.9mm	REV.	
2~5 ±0.25		比例		产品料号	HC-M1254-2510-D539-07	单位	mm
0~2 ±0.15		投影		PART NO.		页次	1/1
Angle ±3.0°		Projection		MATERIAL		SHEET	