








PCB 参考安装方式

NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M4 (M3,M5)
压线螺孔M4 (M3,M5) 可定制
- 3.Current Rating: 60A
额定电流:60A
- 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 1.47 Nm

Ordering Information

HC - * ** * - **** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	D=0.1P	Product No.	Material
Full Teeth (插牙)	0.8mm	M4	0.8mm	0808	0.8mm	07	Copper
Partial Teeth (半插牙)	1.0mm	M4	1.0mm	1010	1.0mm	07	Copper
Full Nut (螺母)	1.2mm	M4	1.2mm	1212	1.2mm	07	Copper
Partial Nut (半螺母)	1.5mm	M4	1.5mm	1515	1.5mm	07	Copper
Full Gasket (垫片)	2.0mm	M4	2.0mm	2020	2.0mm	07	Copper
Partial Gasket (半垫片)	2.5mm	M4	2.5mm	2525	2.5mm	07	Copper
	3.0mm	M4	3.0mm	3030	3.0mm	07	Copper
	3.2mm	M4	3.2mm	3232	3.2mm	07	Copper



			GENERAL TOLERANCE	制 图	07	深圳市华灿天禄电子有限公司			
			DIM TOL	审 核		ShenzhenhuacantianluELECTRONICS CO.,LTD			
			5 or more ±0.35	批 准		产品名称	PCB 焊接端子 厚度1.0 插板 铆垫片	版 本	A
			2~5 ±0.25	APPROVAL		TITLE	M4 4焊脚 8x8x27mm	REV.	
			0~2 ±0.15	比 例		产品料号	HC-RG1044-0808-D337-07	单 位	mm
			Angle ±3.0°	SCALE		PART NO.		页 次	1/1
序号	变更内容	日期		投影		材 料		SHEET	
No.	MODIFY CONTENT	MODIFY DATE		Projection		MATERIAL			