




NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M6 (M4, M5)
压线螺孔M6 (M4, M5) 可定制
- 3.Current Rating: 200A
额定电流:200A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 2.82Nm

Ordering Information

HC - * ** * * - ***** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	Part	Product No.	Material
Welded Teeth (齿牙)	0.01~0.05mm	3.0x3 (螺牙)	(牙脚)	0303~0305mm 0305~0320mm	0307 0307Ag	产品序号	铁质=SPCET (碳钢)
Welded Nut (螺母座)	12mm~25mm	4.0x4 (螺牙)	2个		D1p		RCWeld Coppr (紫铜)
Welded Gasket (垫圈)	2.0~5.0mm	6.0x6 (螺牙)	2个				
	2.0~0.05mm		2个				



工程专用章			GENERAL TOLERANCE		制 图 DRAWING		07		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK							
			5 or more	±0.35	批 准 APPROVAL				产品名称 TITLE	PCB 焊接端子 厚度2.0 插板 铜垫片 M6 6焊脚 18x20x20mm	版 本 REV.	A
1	初版发行		2~5	±0.25	比 例 SCALE				产品料号 PART NO.	HC-RG2066-1820-D915-07	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投 影 Projection				材 料 MATERIAL		页 次 SHEET	1/1