








NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M4 (M3,M5)
压线螺孔M4 (M3,M5) 可定制
- 3.Current Rating: 60A
额定电流:60A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 1.47 Nm

Ordering Information

HC - * ** * - **** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	D=0.1P	Product No.	Material
Full Teeth (插牙)	0.8mm	M4	0.8mm	0808	S=0.1P	默认	Copper
Partial Teeth (半插牙)	1.0mm	M4	1.0mm	1010	S=0.1P	默认	Copper
Partial Teeth (半插牙)	1.2mm	M4	1.2mm	1212	S=0.1P	默认	Copper
Partial Teeth (半插牙)	1.5mm	M4	1.5mm	1515	S=0.1P	默认	Copper
Partial Teeth (半插牙)	2.0mm	M4	2.0mm	2020	S=0.1P	默认	Copper
Partial Teeth (半插牙)	2.5mm	M4	2.5mm	2525	S=0.1P	默认	Copper
Partial Teeth (半插牙)	3.0mm	M4	3.0mm	3030	S=0.1P	默认	Copper
Partial Teeth (半插牙)	3.2mm	M4	3.2mm	3232	S=0.1P	默认	Copper



GENERAL TOLERANCE			制图	07	深圳市华灿天禄电子有限公司			
DIM TOL			审核		ShenzhenhuacantianluELECTRONICS CO.,LTD			
5 or more			批准		产品名称	PCB 焊接端子 厚度1.0 插板 铆垫片	版本	A
2~5			比例		TITLE	M4 4焊脚 8x8x23mm	REV.	
0~2			SCALE		产品料号	HC-RG1044-0808-D338-07	单位	mm
Angle			投影		PART NO.		页次	1/1
序号	变更内容	日期	材料		MATERIAL		SHEET	
No.	MODIFY CONTENT	MODIFY DATE						