




NOTES:

- 备注
- 1.Brass or purple copper,Bright tin-plating
黄铜或紫铜, 镀亮锡
 - 2.Wire screw hole M5
压线螺孔M5
 - 3.Current Rating: 100A
额定电流:100A
 - 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
 - 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information									
HC - * * * * - * * * * - 07									
Type (类型)	Thickness (厚度)	Screw (螺钉)	Welding (焊接)	Series (系列)	Product No. (产品序号)	Material (材料)			
HC-12.5	1.5mm	M5	100	100	14x12x17mm	Brass or Purple Copper (黄铜或紫铜)			



GENERAL TOLERANCE		制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD	
DIM TOL		审核			
5 or more ±0.35		批准		产品名称	PCB 焊接端子 厚度1.5 插板 铜垫片
2~5 ±0.25		比例		TITLE	M5 4焊脚 紫铜 14x12x17mm
0~2 ±0.15		投影		产品料号	HC-RG1554-1412-D712RC-07
Angle ±3.0°		材料		PART NO.	
序号	变更内容	日期		MATERIAL	
No.	MODIFY CONTENT	MODIFY DATE			