








NOTES:
备注

- 1.Brass or purple copper,Bright tin-plating
黄铜或紫铜，镀亮锡
- 2.Wire screw hole M4
压线螺孔M4
- 3.Current Rating: 60A
额定电流:60A
- 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形，毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information									
HC - * ** * - **** - * ** * - 07									
Type Type (Type)	Thickness 0.5~1.0mm 1.0~1.5mm 1.5~2.0mm 2.0~2.5mm 2.5~3.0mm 3.0~3.5mm	Screw Thread M4 (Type) M5 (Type) M6 (Type) M8 (Type) M10 (Type)	Welding Feet 1620±16.20mm	Series 0808±8.08mm	Welding Feet 1620±16.20mm	Product No.	Material Copper (Copper)	Material Copper (Copper)	Material Copper (Copper)



GENERAL TOLERANCE		制 图	07	深圳市华灿天禄电子有限公司	
DIM TOL		审 核		ShenzhenhuacantianluELECTRONICS CO.,LTD	
5 or more ±0.35		批 准		产品名称	PCB 焊接端子 厚度1.0 插板 铆垫片
2~5 ±0.25		APPROVAL		TITLE	M4 4焊脚 8x8x11.2mm
0~2 ±0.15		比 例		产品料号	HC-RG1044-0808-D303-07
Angle ±3.0°		SCALE		PART NO.	
		投 影		材 料	版 本
		Projection		MATERIAL	REV.
					单 位
					UNITS
					页 次
					SHEET