




NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M8 (M5, M6)
压线螺孔M8 (M5, M6) 可定制
- 3.Current Rating: 200A
额定电流:200A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 3.39Nm

Ordering Information

HC	- *	**	*	- ****	- *	***	* - 07
Type Type 1 Tooth (普通型) Type 2 Net (网纹型) Type 3 Net (网纹型)	Thickness 1.0~1.8mm 1.0~1.6mm 1.0~1.5mm 1.0~1.2mm	Screw Thread M4 (螺牙) M4x1 (螺牙) M4x2 (螺牙) M4x3 (螺牙)	Welding Feet 19 (凸角) 19x16 (凸角)	Series 980 (凸角) 1010 (凸角)	[18] IP 9 (凸角) [9] In In p	Product No. 产品序号	Material 材质 (参照)



工程专用章			GENERAL TOLERANCE	制 图 DRAWING	07					 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL	审 核 CHECK								
			5 or more ±0.35	批 准 APPROVAL	产品名称 TITLE	PCB 焊接端子 厚度1.5 插板 铆垫片 MS 6焊脚 22x22x17mm			版 本 REV.	A		
		1	初版发行	2~5 ±0.25 0~2 ±0.15	比 例 SCALE	产品料号 PART NO.	HC-RG1586-2222-D740-07			单 位 UNITS	mm	
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投 影 Projection				材 料 MATERIAL	页 次 SHEET	1/1		