


8

P. C. B LAYOUT



7

6

5

4

3

2

1

参考标准/Standard

UL

IEC

额定电压/Rated voltage

300V

250V

额定电流/Rated current

20A

20A

接触电阻/Contact resistance

20mΩ

绝缘电阻/Insulation resistance

500MΩ/DC500V

使用线径/Wire range

12~26AWG

2.5mm²

耐电压/Wrth standing voltage

AC 2000V/1 Min

机械性能/Mechanical

扭距/Torque:

0.4Nm (3.6Lb. in)

剥线长度/Steip Length:

6-7mm

温度范围/Temp. Range:

-40℃~+105℃

瞬时温度/MAX Soldering

+250℃, for5Sec

尺寸/Dimensions

间距/Pitch:

5.08mm

极数/Poles:

2-24P


0.65

5.08XX

0.65

5.08±0.15


10.50



6.00±0.3

0.80


4.30±0.3



1.00±0.15

5.08(XX-1)

18.00



公差系数表

Tolerance coefficient table model

尺寸范围	公差值
Size range	tolerance value
0-3	±0.1
3-6	±0.12
6-10	±0.14
10-14	±0.16
14-18	±0.19
18-24	±0.22
24-30	±0.25
30-40	±0.28
40-50	±0.32
50-65	±0.37
65-80	±0.43
80-100	±0.50
100-120	±0.57
>120	±0.64

未注角度公差系数表 (GB/T1804-M)

Table of unmarked angle tolerance coefficients

长度分段	第一系列
-10	±1°
>10-50	±30'
>50-120	±20'
>120	±10'

4

焊脚/Pin header

N

Copper alloy, Sn plated

3

方块/Cage

N

Copper alloy, Ni plated

2

螺丝/Screws

N

M3 Steel,Zn plated

1

塑件/Housing

1

PA66, UL94V-0

序号

零件描述/Part description

数量

材料/material

备注 notes

特编型号

Specialized model

特编内容

Special Content

出脚长度

Foot length

单位

unit

比例

proportion

6.0

mm

2:1

尺寸

SIZE

A4

视角

angle of view

⊕

⊞

版本

version

JJ2504

设计

Design

QLY

25/06/05

标准化

standardization

审核

to examine

FJG

25/06/05

工艺

workmanship

批准

approve

NHB

25/06/05

共1张

1 sheet in total

东莞市文章济美电子有限公司

model

JME129-5.08-XXP-00A1-B

声明: 本图纸知识产权归宁波佳绩机电科技有限公司所有, 未经允许私自传播、盗用须承担法律责任。 Disclaimer: The intellectual property rights of this drawing belong to Ningbo Jingju Electromechanical Technology Co., Ltd. Unauthorized dissemination or theft shall bear legal responsibility.