



PCB 参考安装方式

NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M4(M3,M5)
压线螺孔M4(M3,M5)可定制
- 3.Current Rating: 70A
额定电流:70A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
- 6.扭矩: 1.47 Nm

Ordering Information

HC - * ** * - **** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	D=0.1P	Product No.	Material
Full Teeth (插牙)	0.8mm	M4 (螺牙)	0.8mm	0808x8mm	S=0.1P	默认=07	Copper
Full Nut (螺螺母)	1.2mm	M4 (螺牙)	1.2mm	1208x12mm	S=0.1P	产品序号	(黄铜)
Full Gasket (螺垫片)	1.5mm	M4 (螺牙)	1.5mm	1508x15mm	S=0.1P		Red Copper
	2.0mm	M4 (螺牙)	2.0mm	2008x20mm	S=0.1P		(紫铜)
	2.5mm	M4 (螺牙)	2.5mm	2508x25mm	S=0.1P		
	3.0mm	M4 (螺牙)	3.0mm	3008x30mm	S=0.1P		
	3.2mm	M4 (螺牙)	3.2mm	3208x32mm	S=0.1P		



		GENERAL TOLERANCE	制 图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
		DIM TOL	审 核				
		5 or more ±0.35	批 准		产品名称	PCB 焊接端子 厚度1.0 插板 铆垫片	版 本
		2~5 ±0.25	APPROVAL		TITLE	M4 4焊脚 12x9x16.2mm	REV.
		0~2 ±0.15	比 例		产品料号	HC-RG1044-1209-D336-07	单 位
		Angle ±3.0°	SCALE		PART NO.		UNIT
序号	变更内容	日期	投 影		材 料	页 次	
No.	MODIFY CONTENT	MODIFY DATE	Projection		MATERIAL	SHEET	1/1