







NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜或紫铜, 镀锡
- 2.Wire screw hole M4 (M3, M5)
压线螺孔M4 (M3, M5) 可定制
- 3.Current Rating: 80A
额定电流:80A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 1.47Nm

Ordering Information

HC - * ** * - **** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	Welding Feet	Product No.	Material
HC=Full Tooth (插牙) RT=Hivet Nut (铆螺母) RT=Hivet Gasket (铆垫片)	0.5~1.0mm 1.0~1.5mm 1.5~2.0mm 2.0~2.5mm 2.5~3.0mm 3.0~3.5mm	3~6 (螺牙) 3~6 (螺牙) 3~6 (螺牙) 3~6 (螺牙) 3~6 (螺牙) 3~6 (螺牙)	2~4 (焊脚) 2~4 (焊脚) 2~4 (焊脚) 2~4 (焊脚) 2~4 (焊脚) 2~4 (焊脚)	0808688mm 1620~16x20mm	W=100P S=50RT D=100P Dip	Product No. 产品序号	Material 默认=铜 (黄铜) RT=Red Copper (紫铜)



工程专用章

GENERAL TOLERANCE			制 图	07	深圳市华灿天禄电子有限公司			
DIM TOL			审 核		ShenzhenhuacantianluELECTRONICS CO.,LTD			
5 or more			批 准		产品名称	PCB 焊接端子 厚度1.2 插板 铆垫片	版 本	A
2~5			APPROVAL		TITLE	M4 4焊脚 11.5x11.5x11mm	REV.	
0~2			比 例		产品料号	HC-RG1244-1111-D540-07	单 位	mm
Angle			SCALE		PART NO.		UNITS	
序号	变更内容	日期	投 影		材 料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection		MATERIAL		SHEET	