







NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M3 (M4,M5)
压线螺孔M3 (M4,M5) 可定制
- 3.Current Rating: 50A
额定电流:50A
- 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 0.79Nm

Ordering Information

HC - * ** * - **** - * ** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	WOP	Product No.	Material
Pin (插针)	0.8mm, 0.9mm, 1.0mm, 1.2mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm	M3 (螺牙), M4 (螺牙), M5 (螺牙)	2mm, 3mm, 4mm, 5mm, 6mm, 8mm	08080808, 16201620mm	WOP	产品序号	默认Copper (黄铜), Red Copper (紫铜)



GENERAL TOLERANCE			制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
DIM TOL			审核		产品名称	PCB 焊接端子 厚度0.8 侧插 铜垫片	版本	A
5 or more ±0.35			批准		TITLE	M3 4焊脚 8.8x11.2x11.5mm	REV.	
2~5 ±0.25			比例		产品料号	HC-RG0834-0811-FD207-07	单位	mm
0~2 ±0.15			投影		PART NO.		页次	1/1
序号	变更内容	日期	投影		MATERIAL		SHEET	
No.	MODIFY CONTENT	MODIFY DATE	Projection					