




- NOTES:  
备注
- 1.Brass or purple copper,Bright tin-plating  
黄铜或紫铜，镀亮锡
  2. Wire screw hole M5  
压线螺孔M5
  - 3.Current Rating: 70A  
额定电流:70A
  4. There shall be no defects such as pin deformation and burrs.  
不得有脚变形，毛刺等缺陷
  - 5.Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差

| Ordering Information              |           |             |          |              |         |             |           |  |  |
|-----------------------------------|-----------|-------------|----------|--------------|---------|-------------|-----------|--|--|
| HC - * ** * - **** - * *** * - 07 |           |             |          |              |         |             |           |  |  |
| Type                              | Thickness | Screw       | Welding  | Series       | S-01P   | Product No. | Material  |  |  |
| M+11 Teeth                        | 08-0.8mm  | 3-63 (螺牙)   | 10-1.0mm | 1620-16x20mm | S-SMT   | 产品序号        | 默认-Copper |  |  |
| 08-0.8mm                          | 10-1.0mm  | 4-84 (螺牙)   | 12-1.2mm | 1620-16x20mm | FD-Flap |             | (黄铜)      |  |  |
| 12-1.2mm                          | 15-1.5mm  | 5-95 (螺牙)   | 15-1.5mm | 1620-16x20mm | 01g     |             | (紫铜)      |  |  |
| 15-1.5mm                          | 20-2.0mm  | 6-106 (螺牙)  | 20-2.0mm | 1620-16x20mm |         |             |           |  |  |
| 20-2.0mm                          | 25-2.5mm  | 8-127 (螺牙)  | 25-2.5mm | 1620-16x20mm |         |             |           |  |  |
| 25-2.5mm                          | 30-3.0mm  | 10-148 (螺牙) | 30-3.0mm | 1620-16x20mm |         |             |           |  |  |
| 30-3.0mm                          | 32-3.2mm  | 12-169 (螺牙) | 32-3.2mm | 1620-16x20mm |         |             |           |  |  |



|       |                |             |                   |            |    |                                                          |                       |       |     |
|-------|----------------|-------------|-------------------|------------|----|----------------------------------------------------------|-----------------------|-------|-----|
| 工程专用章 |                |             | GENERAL TOLERANCE | 制 图        | 07 | 深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianluELECTRONICS CO.,LTD |                       |       |     |
|       |                |             | DIM TOL           | 审 核        |    | 产品名称                                                     | PCB 焊接端子 厚度1.2 贴片 抽牙  | 版 本   | A   |
|       |                |             | 5 or more ±0.35   | 批 准        |    | TITLE                                                    | M5 4焊脚 40x10x7.9mm    | REV.  |     |
|       |                |             | 2~5 ±0.25         | APPROVAL   |    | 产品料号                                                     | HC-M1254-4010-S526-07 | 单 位   | mm  |
|       |                |             | 0~2 ±0.15         | 比 例        |    | PART NO.                                                 |                       | UNITS |     |
|       |                |             | Angle ±3.0°       | SCALE      |    | 材 料                                                      |                       | SHEET | 1/1 |
| 1     | 初版发行           |             |                   | 投 影        | ⊕  | MATERIAL                                                 |                       |       |     |
| 序号    | 变更内容           | 日期          |                   | Projection |    |                                                          |                       |       |     |
| No.   | MODIFY CONTENT | MODIFY DATE |                   |            |    |                                                          |                       |       |     |