





备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M4(M5,M6)
压线螺孔M4(M5,M6)可定制
- 3.Current Rating: 70A
额定电流:70A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 1.47 Nm

Ordering Information

HC - * ** * * - ***** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	IP	Product No.	Material
Full Teeth	080, 8mm	5×5 (螺牙)	4个	08080808mm	S-SHT		默认=Copper (黄铜)
160, 12mm	5×5 (螺牙)	4个	16001612mm	PUM	1P		PC=Al (铝合金)
120, 12mm	5×5 (螺牙)	4个				产品序号	
150, 15mm	5×5 (螺牙)	4个					
200, 20mm	6×6 (螺牙)	4个					
250, 25mm	6×6 (螺牙)	4个					
300, 30mm	6×6 (螺牙)	4个					
10= Rivet Gasket (铆垫片)							



			GENERAL TOLERANCE	制 图 DRAWING	07	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK		产品名称 TITLE	PCB 焊接端子 厚度1.2 插板 抽牙 M4 4焊脚 10x8x17mm	版 本 REV.	A
			5 or more ±0.35	批 准 APPROVAL					
1	初版发行		2~5 ±0.25	比 例 SCALE		产品料号 PART NO.	HC-M1244-1008-D536-07	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投 影 Projection		材料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						

