

1.材料和电镀\Materials and Finishes:

外 壳\Body - 黄铜\Brass,镀镍\Nickel plating

内导体>Contact - 磷铜\Phosphor copper,镀金\Gold plating

绝缘体\Insulator - 聚四氟乙烯\Teflon,本色\Natural

2.电气性能\Electrical:

A.特性阻抗\Impedance:50 Ohm




B.使用频率\Frequency range:DC - 4GHz

C.介质耐压\Breakdown voltage:1000V rms

D.绝缘电阻\Insulation resistance:5000 MΩ

3.机械性能\Mechanical:

A.使用寿命\Durability:500 cycles



 询价发货: (86)13342983566 (86)13342985799 (86)18938914766 技术支持: (86)13975145315 E-mail : sales@cntitle.net			版次		比例		3:1		料 号	CT4.1.70	
			第一角法						规 格	BNC-KF	
			1.未注公差按ISO2768-1(m) 2.去尽毛刺C0.13max 3.各圆同轴度Ø0.1max						名 称	BNC母头四孔法兰式	
									*尺寸为重要尺寸		单位
设 计	JAT	2026.08.31									
审 核	DF	2026.08.31									
批 准	DF	2026.08.31									