


BIN ASSIGNMENT

B

- 1.Current rated: 1.5A
- 2.Voltage rating: 30V AC/DC
- 3.Dielectric withstanding Voltage:500V AC
- 4.Contact resistance: 30mΩ Max
- 5.Insulation resistance: 1,000MΩ Min
- 6.Mating force: 35N Max
- 7.Unmating force: 10N Min
- 8.Terminal Retention: 1.2kgf Min
- 9.Durability cycle:5,000(SUS) cycles
- 10.Operating temperature: -40°C ~ +85°C
- 11.Waterproof grade: IPX7



4-1.1C

E



RoHS
Compliant
EU RoHS Standards

SIZE:

Molde Code: GT-3AF001B-DSNNXX-48

Liu

Xla

Cher

2025.08.08

®

REV: A0

SHEET: 1/1