



1P 2P



Notes:

Rated current:3.0A

Withstand Voltage:500V AC/DC

Contact Resistance:20mΩ Max


Insulation Resistance:1000MΩ Min

Operating Temperature:-40℃ TO +105℃

Contact Material:Brass

Plating:G/F

Insulator Material: PA6T UL94V-0 BK



RECOMMENDED PCB LAYOUT (TOP VIEW)

TOLERANCES:±0.05

NO.	DATE	DESCRIPTION	APPROVAL	DRAWING:	GENERAL TOLERANCE		东莞市文章济美电子有限公司	
				MAO ZI HAO	.X: ±0.30	.X*: ±2°		
1	24-04-18	初次发行	Jack	CHECKED:	.XX: ±0.20	.XX*: ±1°	DESCRIPTION: FH2.54*8.5 1*NP PC3.0 180°Y型端	
2				YAO HUI SONG	.XXX: ±0.10	.XXX*: ±0.5°		
3				APPROVAL:	UNIT: MM	PROJECTION	PART NO: 5001-050294-B	
4				HAN XIAO QIU	SCALE: N/A			
5					SHEET: 1/1		SERIES :	
							REC:1.0	
							ROHS	