












Recommend of PC Board Holes
Tolerance : ± 0.05 (Top view)




MATE PLUG Ø7.40



NOTES:

- VOLTAGE RATING: 20V DC ;
- CURRENT RATING: 15A ;
- CONTACT RESISTANCE: $\leq 30m\Omega$;
- INSULATION RESISTANCE: $\geq 100M\Omega$;
- WITHSTAND VOLTAGE: 500 VAC ;
- UNMATING FORCE: 3N~20N ;
- OPERATING LIFE: 5000 CYCLES MIN ;
- OPERATION TEMPERATURE: $-20^{\circ}C \sim +70^{\circ}C$;



Ordering Information

HC- DC*** - * - * ** - * - * - * - 08

序列号	Nature	Foot	Type	T=Through holes	PIN Diameter	Material
M=Male	2=2P	DP=DP (0.8)	DP=DP (0.8)	1.3=1.3mm	HT=HT	
F=Female	3=3P	SM=SM (0.8)	SM=SM (0.8)	1.6=1.6mm	M=M	
	4=4P	VS=Vertical SMT (0.8)	VS=Vertical SMT (0.8)	2.0=2.0mm		
		MM=Mid Mount (0.8)	MM=Mid Mount (0.8)	2.5=2.5mm		
		DS=DS=SM (0.8)	DS=DS=SM (0.8)			
		WB=Wire Bonding (0.8)	WB=Wire Bonding (0.8)			

6		中心针	C2680	1	镀金/镀锡	
5		正极针	C7025	1	镀金	
4		负极长针	C7025	1	镀金	
3		负极短针	C7025	1	镀金	
2		屏蔽外壳	C2680	1	镀镍	
1		主体	PA10T	1	黑色	
序号	零件料号	名 称	材 料	数量	镀层/颜色	备 注

1	初版发行	
序号	变更内容	日期
No.	MODIFY CONTENT	MODIFY DATE

GENERAL TOLERANCE	制 图
DIM	DRAWING
TOL	审 核
	CHECK
X.X	批 准
	APPROVAL
X.XX	比 例
	SCALE
X.XXX	投 影
Angle	Projection
$\pm 3.0^{\circ}$	

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO., LTD

产品名称	电源插座 母座 9P 卧插	版 本	A
TITLE	05.0 全铜	REV.	
产品料号	HC-DC7406-F-9DIP-5.0-HT-08	单 位	mm
PART NO.		UNIT	
材料		页 次	1/1
MATERIAL		SHEET	