








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.5	阿树

SPECIFICATIONS:
Temperature range: -30~+70℃
RATING: DC 30V 0.5A
Contact resistance: ≤30mΩ
Insulation resistance: ≥100MΩ DC250V
Withstanding voltage: AC 500V
Plugging force: 3~20N
Life Test: 5000次



SCHEMATIC	
Model	DC-0330-SMT
Center pin	ø1.00mm
	ø1.30mm
	ø1.65mm

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: DC POWER JACK		
CHECKED		UNIT: mm/in		PART NO.: DC-0330-1.65-SMT		
APPROVED		SIZE: A4		DWG NO.: X-DC-0330-1.65-SMT		
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1

XKB INDUSTRIAL PRECISION CO.,LIMITED