



REV.	ECN. NO.	APPD.
A		

NOTES.
Rated Current:1.0AMP.
Contact Resistance:20m Ω Max.
Withstand Voltage:500V AC/DC
Insulation Resistance:1000M Ω Min.
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:PA9T+30%G.F UL94V-0 BK





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)



Ordering Information

MTP315-11XX S1

No.of Pins per
Row: 01~40



X. $\pm$ 0.30	X.° $\pm$ 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.		
.X $\pm$ 0.20	.X° $\pm$ 2°	MAT'L	PART NO.(INTENDED USE)	TITLE: PH1.27 SINGLE ROW 180° H=1.5		
.XX $\pm$ 0.10	.XX° $\pm$ 1°	FINISH	APPD: SUNNY	DWG NO.: MTP315-11XXS1		
.XXX $\pm$ 0.05	.XXX° $\pm$ 0.5°	Q'TY	CHKD: LISA			
PIN HEADER CONNECTOR			DR: ZOE 2006-11-28			
				SCALE	SHEET	REV.
				1/1	1/1	A