





RoHS Compliant



PCB LAYOUT
(所有尺寸公差为±0.05)



3	NAIL	C2680R-EH	2PCS
2	TERMINAL	C5191R-EH	3PCS
1	HOUSING	LCP	1PCS
ITEM	NAME	MATERIAL	Q'TY

NOTES:

1) FINISH:

- 1-1 CONTACT: 1u"MIN GOLD PLATING ON CONTACT AREA
1u"MIN GOLD PLATING ON SOLDER TAILS
50u"MIN. NICKEL UNDERPLATING OVER ALL
1-2 NAIL: 50u"MIN NICKEL UNDERPLATING,
100~200u" TIN OVERALL


2) ELECTRICAL SPECIFICATIONS:

- 2-1 VOLTAGE RATING: 250V
2-2 CURRENT RATING: 2A
2-3 INSULATION RESISTANCE: 500MEG.OHM MIN
2-4 CONTACT RESISTANCE: 50 MILL.OHM MAX
2-5 OPERATION TEMPERATURE: -20° TO +85°
2-6 DURABILITY: 5000 CYCLES
2-7 NORMAL FORCE: 90gf MIN AT THE WORKING

POSITION

3) DIMENSIONS WITH MARK " * " MUST BE MEASURED BY QC AND IPQC

6.20	4.50
6.00	4.30
5.70	4.00
5.40	3.70
DIM A	DIM B



深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	3.0PH 3P 侧压电池座 有柱外焊		
		料号 (PART NO)	MLD-BAT03P-30XXW		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	版次 (REV): A/0	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1		模号 (MODEL NO)	MLD-2509031032	审核 (CHECKED)	邱敏
		图号 (DWG NO)		核准 (APPROVED)	陈镇