



RoHS Compliant



PIN NO.	PIN Assignmeng.
PIN1	DAT2
PIN2	CD/DAT3
PIN3	CMD
PIN4	VDD
PIN5	CLK
PIN6	Uss2
PIN7	DAT0
PIN8	DAT1

NOTES:

1.MATERIAL:

- 1).HOUSING MATERIAL:THERMOPLASTIC UL94V-0;COLOR:BLACK
- 2).CONTACT MATERIAL:COPPER ALLOY,T=0.15mm
- 3).SHELLMATERIAL:STATILESS STEEL,T=0.20mm

2.FINISH:

- 1).CONTACT FINISH:50u"min.NICKEL UNDER PLATED,PLATED 3u"Au ON CONTACT AREA;TIN-PLATED HIGH-TEMPER ATURR 80u"-120u" ON SOLDER AREA.
- 2).SHELL FINISH:Cleaning.

3.ELECTRICAL SPECIFICATIONS:

- 1).OPERATING VOLTAGE: 250V(AC/DC).
- 2).CURRENT RATING: 0.5A.
- 3).OPERATING TEMPERATURE: -20°C~+65°C.
- 4).INSULATION RESISTANCE: 1000M OHMS min. at 250VDC.
- 5).DIELECTRIC WITHSTANDING VOLTAGE:500VAC/1minute.
- 6).CONTACT RESISTANCE:100m OHMS max.

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	SIM 6P 连桥带档 2.2H		
		料号(PART NO)	MLD-SIM-6P-H2.2		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/O	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)	图号 (DWG NO)	审核 (CHECKED)	邱敏
				核准(APPROVED)	陈镇