








RoHS Compliant



RECOMMENDED PCB LAYOUT
TOLERANCE=±0.05



CIRCUIT DIAGRAM

- NOTES: 1.MATERIAL:
HOUSING:LCP(UL 94V-0)
TERMINAL:PHOSPHOR BRONZE,T=0.25mm
- 2.PLATING:
TERMINAL:
SEE ORDERING INFORMATION
- 3.RATING:
OPERATING VOLTGE:50V(AC/DC)
CURRENT RATING:0.5A(AC/DC)
OPERATING TEMPERATURE:-20°C~+85°C
DURABILITY:5000 CYCLES
INSERTED FORCE:0.22~2.22KGS
WITHDRAWAL FORCE:0.22~2.22KGS
- 4.PRODUCT ACCORD WITH ROHS OF EUROPE

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	3.5mm H4.5 6P 斜口全贴		
		料号(PART NO)	MLD-PJ-0148		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/O	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10	模号 (MODEL NO)		审核 (CHECKED)	邱敏
	X" ± 5" X.X" ± 2"	图号 (DWG NO)		核准(APPROVED)	陈镇