





RoHS Compliant



Recommended PCB Layout

备注

1. 材质:

1.1 胶芯: LCP UL94V-0

1.2 端子: 磷铜, 半金锡, 触点镀金 0.5μ ", 零锡 $50-80U$ "

1.3 外壳: SUS, 镍底 30μ ", 焊引脚镀金 0.5μ "

2. 主要特性:

2.1 额定电流: 0.5A

2.2 接触阻抗: $50m\Omega$ MAX

2.3 绝缘阻抗: $100M\Omega$ MIN 100V DC

2.4 耐压测试: 100V AC

2.5 沾锡性: 温度 $235\pm 5^{\circ}C$, 时间 $5\pm 0.5s$

2.6 单PIN正向应力: $0.035kgf$ MIN

2.7 使用寿命: 1000次

2.8 耐湿性: 烤箱测试: 温度 $250\pm 5^{\circ}C$, 时间2分钟

2.9 工作环境: 温度: $-30^{\circ}C \sim +80^{\circ}C$; 湿度: 80% MAX

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	SIM 6P 连桥有挡1.8H		
		料号(PART NO)	MLD-SIM-6P-H1.8		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)		审核 (CHECKED)	邱敏
 		图号 (DWG NO)		核准(APPROVED)	陈镇
			MLD-2509031032		