






RoHS Compliant



Recommended PCB Layout

备注:

1. 材质:

1.1 胶芯: LCP UL94V-0

1.2 端子: 磷铜, 半金锡, 触点镀金1 μ ", 雾锡80U"

1.3 外壳: SUS, 镍底50 μ ", 焊接脚镀金1 μ "

2. 主要特性:

2.1 额定电流: 0.5A

2.2 接触阻抗: 50m Ω MAX

2.3 绝缘阻抗: 100M Ω MIN 100V DC

2.4 耐压测试: 100V AC

2.5 沾锡性: 温度235 $\pm$ 5 $^{\circ}$ C, 时间5 $\pm$ 0.5s

2.6 单PIN正向应力: 0.035kgf MIN

2.7 使用寿命: 1000次

2.8 耐温性: 烤箱测试: 温度250 $\pm$ 5 $^{\circ}$ C, 时间2分钟

2.9 工作环境: 温度: -30 $^{\circ}$ C~+80 $^{\circ}$ C; 湿度: 80% MAX

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	SIM 6P 连桥有档1.5H		
		料号(PART NO)	MLD-SIM-6P-H1.5		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X $\pm$ 0.38 X.XX $\pm$ 0.20 X.XXX $\pm$ 0.10 X" $\pm$ 5" X.X" $\pm$ 2"	模号 (MODEL NO)		审核 (CHECKED)	邱敏
 		图号 (DWG NO)		核准(APPROVED)	陈镇