

Wire Wound Type Common Mode Filter

CND-tek


磁联达

- 1.High common mode impedance at high frequency cause excellent noise suppression performance.
- 2.WCM4532F2SF series realizes small size and low profile.4.5x3.2x2.8mm.
- 3.100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 4.Operating temperature : -40 to +125 °C
- 5.Storage temp. and humidity : -40 to +125 °C




Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	Withstand Volt. (Vdc) max.	IR (Ω) min.
WCM4532F2SF-800T30-CND	80±25%	100	0.05	3000	50	125	10M
WCM4532F2SF-900T30-CND	90±25%	100	0.05	3000	50	125	10M
WCM4532F2SF-121T30-CND	120±25%	100	0.05	3000	50	125	10M
WCM4532F2SF-201T15-CND	200±25%	100	0.10	1500	50	125	10M
WCM4532F2SF-601T15-CND	600±25%	100	0.24	1500	50	125	10M
WCM4532F2SF-801T10-CND	800±25%	100	0.24	1000	50	125	10M

MECHANICAL




SUGGEST LAYOUT








SCHEMATICS




IMPEDEANCE FREQUENCY



Dimension: mm




TAPING AND PACKING



IND1752-J-E

Reel



Quantity (pcs):

500 PCS PER REEL
4 REELS PER CARTON
2000PCS PER CARTON

Dimensions in mm

Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
Tel:0755-27652992 29016433 E-mail: sales1@cd-tek.com Website:www.cd-tek.com