







RoHS Compliant



IR前	0.08
IR后	0.10



- (1):Rated Voltage: 60 V AC . ;
(2):Contact Resistance:20mOHM Max. ;
(3):Dielectric Withstanding Voltage:100V AC For 1 Minute;
(4):Insulation Resistance:1000M OHM Min. ;
(5):Frequency Range: DC up to 6GHz
VSWR: 1.3 max. at 0~3GHz;
VSWR: 1.4 max. at 3~6GHz;
(6):Operating Tempersture: -40℃ to +90℃
(7):Durability: 30 cycles
(8):REC Connector shall stand IR reflow twice
(9):▼As the focus control size

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	SHELL	1	COPPER ALLOY	Au plated over Ni
2	Housing	1	High Temp.Plastic	Black UL94V-0
3	CONTACT	1	COPPER ALLOY	Au plated over Ni

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.			品名(ITEM NO)	RF一代板端天线座	
			料号(PART NO)	MLD-U.FL-IPEX1	
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)		审核 (CHECKED)	邱敏
		图号 (DWG NO)		核准(APPROVED)	陈镇

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE±0.05