




REV.	ECN NO OR DESCRIPTION	REVISED	DATE
B	PROPOSE ONLY	ALLEN	2018.10.18



RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)
RECOMMENDED MATAL MASK T=0.12MM
NO PATTERN AREA
(TOLERANCE: ±0.05)

(NOTE)
MATERIAL:

Insulator: High Temperature Thermoplastic
Contact: Copper Alloy
Shell: STAINLESS

PLATING:

Contact: Plated 30u" Ni Overall Contact G/F
Shell: Plated 30u" Ni Overall
Plated G/F Selective Contact Area


Electrical:

Current Rating :0.5mA max.
Voltage Rating :50V DC MAX
Ambient Temperature Range :-20°C~+85°C
Storage Temperature Range :-40°C~+70°C
Ambient Humidity Range :95% R.H. Max.
Contact Resistance:100m max.
Insulation Resistance:1000M min./250V DC
Dielectric Withstanding Voltage:500V AC
Mating Cycles:5,000 Insertions
Temperature: 260°C ±5°

6. PART No.:

MS 0 PP - 13 00 06- 13 G

MicroSIM CON-
0=WITHOUT POST
PP=PUSH Type.
13:HEIGHT 1.35mm
C=gold plating on contact
13=Product Order
Pin NO. 6=6Pin
00=NORMAL TYPE.(ON PCB)



MicroSIM CARD

Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	VPP
C7	I/O
C8	Reserved

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	HOUSING	1	Hi-temp Thermoplastic	Black UL94V-0
2	DATA CONTACT	6	Copper Alloy	Contact area:Gold plated
3	SHELL	1	Stainless Steel	SMT area:Gold plated
4	COIL SPRING	1	SWP	
5	HEART CAM	1	Hi-temp Thermoplastic	Black UL94V-0
6	CAM PIN	1	Stainless Steel	

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.5 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10




深圳市精睿兴业有限公司
SHENZHEN KRCONN TECHNOLOGY CO., LTD

TITLE	1.35mm (Detect)Push Micro SD CARD CONN.
DWN	ALLEN
CHKD	KEVIN
APVD	ERIC.W
PART NO.	MSOPP-130006-13G
SCALE:1:1	UNIT: mm
SIZE: A3	SHEET:10F 1
REV: B	


CUSTOMER COPY

REV.	ECN NO OR DESCRIPTION	REVISED	DATE
B	PROPOSE ONLY	ALLEN	2018.10.18




NOTES

1. NUMBER OF CONNECTORS:1000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY:10000PCS/CARTON



将10卷产品放入箱内

UNLESS OTHERWISE SPECIFIED TOLERANCES		 深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD				
DECIMALS:	ANGLES:	TITLE	1.35mm (Detect)Push Micro SD CARD CONN.			
X :±0.5	X :±2°	DWN	ALLEN	PART NO. MSOPP-130006-13G		
X.X :±0.20	X.X :±1°	CHKD	KEVIN	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	ERIC.W	SIZE: A3	SHEET:10F 1	REV: B
		CUSTOMER COPY				