





RoHS Compliant





NOTES:

1. CONTACT CURRENT RATING: 1A.
2. CONTACT RESISTANCE: 50 mΩ MAX.;
3. INSULATION RESISTANCE: 1000Ω MIN.;
4. DIELECTRIC WITHSTANDING: 500V AC MIN.;
5. DURABILITY: 5,000 CYCLES MIN.;
6. CONNECTOR MATING FORCES: 29.4N (3.00Kgf) MAX.;
7. CONNECTOR UNMATING FORCES: 2.94N(0.30Kgf) MIN.;
8. PRODUCT MEET THE REQUEST OF THE RoHs, SEE TABLE A:

TABLE A:

7	HOUSING	1	HIGH TEMPERATURE UL 94-V0 BLACK
6	CONTACT 6	1	COPPER ALLOY/CONTACT AREA GOLD PLATED
5	CONTACT 5	1	COPPER ALLOY/CONTACT AREA GOLD PLATED
4	CONTACT 4	1	COPPER ALLOY/CONTACT AREA GOLD PLATED
3	CONTACT 3	1	COPPER ALLOY/CONTACT AREA GOLD PLATED
2	CONTACT 2	1	COPPER ALLOY/CONTACT AREA GOLD PLATED
1	CONTACT 1	1	COPPER ALLOY/CONTACT AREA GOLD PLATED
ITEM	NAME	Q'TY	MATERIAL / FINISH



电路原理图

RECOMMENDED PCB LAYOUT
TOLERANCES ±0.05(TOP VIEW)

深圳市敏连达科技有限公司
Shenzhen Minlianda Technology Co.,Ltd.

品名(ITEM NO) ϕ 3.5 H4.7斜口板上型

料号(PART NO) MLD-PJ-0045

单位(UNIT): MM

未注公差
TOLERANCE UNSPECIFIED

版次(REV): A/0

页次(PAGE):1/1

设计 (DESIGN)

柯南

比例(SCALE) 1:1

X.X ± 0.38
X.XX ± 0.20
X.XXX ± 0.10
X" ± 5"
X.X" ± 2"

模号 (MODEL NO)

图号 (DWG NO)

审核 (CHECKED)

邱敏

MLD-2509031032

核准(APPROVED)

陈镇