






RoHS Compliant



RECOMMENDED PCB LAYOUT
(Witchout Post)

SPECIFICATION

1. MATERIAL
HOUSING:HI-TEMP PLASTIC UL 94V-0;BLACK
CONTACT:COPPER ALLOY
SHELL:STAINLESS STEEL
2. ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING:0.5 AMPERES.
DIELECTRIC WITHSTANDING VOLTAGE:AC500V R. M. S.
INSULATION RESISTANCE:500 M Ω MIN.
CONTACT RESISTANCE:40 M Ω MAX.
3. ENVIRONMENTAL
OPERATING TEMPERATURE:-25° C~+90° C
4. ENVIRONMENTAL
MATING CYELES:3000 INSERTIONS
5. MECHANICAL CHARACTERISTICS
CARD PUSH INSERTION/OUT FORCE:0.7~1.20KGF
CONTACT SEPARATION FORCE:0.20KGF MIN.

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	TF 抽屉式1.5H 无柱		
		料号(PART NO)	MLD-TF-015		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	版次(REV): A/O	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1		模号 (MODEL NO)		审核 (CHECKED)	邱敏
 		图号 (DWG NO)		核准(APPROVED)	陈镇
			MLD-2509031032		