







RoHS Compliant



PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)



NOTES:

- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
COVER: COPPER ALLOYS OR STEEL.
- 2.PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: GOLD OVER NICKEL.
SOLDER AREA: TIN OVER NICKEL.
- 3.MULTIMEDIA CARD COMPATIBLE

RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	TF PUSH 外焊双压片		
单位(UNIT): MM		料号(PART NO)	MLD-TF PUSH-H1.8		
比例(SCALE) 1:1		版次(REV): A/O	页次(PAGE):1/1	设计 (DESIGN)	柯南
TOLERANCE UNSPECIFIED		模号 (MODEL NO)	审核 (CHECKED)		
X.X ± 0.38		图号 (DWG NO)	MLD-2509031032	核准(APPROVED)	陈镇
X.XX ± 0.20					
X.XXX ± 0.10					
X" ± 5"					
X.X" ± 2"					