





SPECIFICATION:

1.MATERIAL:

HOUSING:LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680R-H,T=0.25mm

2.FINISH:

CONTACT:1u",3u",5u",15u"30u"GOLD PLATING ON CONTACT AREA

100u" MIN.TIN PLATING ON SOLDERTAILS

40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:


CURRENT RATING:1.5 AMPERE PER CONTACT

CONTACT RESISTANCE:30 MILLIOHMS MAX

INSULATION RESISTANCE:1000 MEGOHMS MIN

DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40°C ~ +85°C



P.C.B Layout

环境要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-SATA-02-22PXTG		版本 REV.	A	
2	Terminal	BRASS C2680R-H		Gold/Tin Plated				X. ±0.30	X.* ±3°	审核 CHECK	LEO			品名 TITLE	SATA 7+15P 夹角插座 夹板1.0七孔		页次 SHEET	1/1	
1	Housing	High Temp	Black	UL 94V-0				X.X ±0.20	X.X* ±2°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.					
								X.XX ±0.05	X.XX* ±0.5°					单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK															
1		2		3		4		5		6		7		8		9			