










SPECIFICATION:

1.MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLD PLATING

ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
3	Peg	Brass C2680R		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE

GENERAL TOLERANCE	
X.	±0.30
X.X	±0.20
X.XX	±0.05

制图 DRAWING
审核 CHECK
批准 APPROVAL
单位 UNITS

ROSE
LEO
JOHN
MM
比例 SCALE
1:1

料号 PART NO.	ZX-SATA-05-22PXTM	版本 REV.	A
品名 TITLE	SATA 7+15P 单排脚直立式180°(散置款)	页次 SHEET	1/1
客户料号 CUTM.NO.			
兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			