





RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05



NOTES:

1.MATERIAL:

HOUSING:LCP 30% G/F UL94V-0
COLOR:BLACK

CONTACT:BRASS T=0.25mm

2.FINISH:

CONTACT:GOLD FLASH PLATING ON CONTACT AREA

100u"MIN.TIN PLATING ON SOLDER TAILS

50u"MIN.NICKEL UNDERPLATING OVER ALL

BOARD LOCK:100u"MIN.TIN PLATING ON SOLDER TAILS

50u"MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:


CURRENT RATING:1.5 AMPERE PER CONTACT

CONTACT RESISTANCE:30 mΩ MAX

INSULATION RESISTANCE:1000 MΩ MIN

DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40°C ~ +85°C



环保要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-SATA-01-15PSZG	版本 REV.	A
3	Peg	Brass C2680		Tin/Ni Plated				X.±0.30	X.*±3°	审核 CHECK	EVA		品名 TITLE	SATA 15P公座90度DIP型带侧弯针长2.30mm	页次 SHEET	1/1
2	Terminal	Brass C2680		Gold/Tin Plated				.X±0.20	.X*±2°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
1	Housing	High Temp	Black	UL 94V-0				.XX±0.05	.XX*±0.5°		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK												